



HIGH QUALITY
MADE IN GERMANY



MINING CABLES


Product Overview



The planet's pathways

WHERE SUSTAINABILITY MEETS INNOVATION

Pioneering Cable Solutions
for a Brighter Future



At Prysmian, sustainability is the driving force behind everything we do. Our eco-friendly cable solutions minimise environmental impact while perfectly aligning with our customers' needs. We're leading the charge in green innovation, optimising operations for resource efficiency and promoting responsible practices throughout our supply chain. Prysmian isn't just about making cables, it's about crafting a sustainable future in technology.

Join us in our quest for a greener world, where technology and environmental responsibility go hand in hand.

5,600+

patents covering the main innovations

298

Product families launched during the year

26

Research centres

900

Professionals

50+

Collaborations with research centres and universities

WHAT WE OFFER


Elastomeric cables are the natural choice for applications where durability, flexibility, and safe operation under extreme conditions are important. Prysmian's elastomeric cables have been "field proven" in thousands of operations, and with continuous development, utilise the best features of cables offered around the world.

Prysmian has developed extensive know-how over many years regarding the special operational conditions of mining equipment. The decisive factor was close cooperation with many significant mining operators. The experience we gain every day contributes to the design of our cables. The high operational reliability and service life of our cable solutions are based on this experience.








THE FORCE WILL BE WITH YOU.

TENAX-LUMEN
– our self-luminous cable
safely bring power to your
mobile mining equipment.

TENAX-LUMEN self-luminous power cable is like a modern version of the canary in a coal mine, adding safety to miners and equipment. This extremely robust trailing cable supplies power to large mobile mining equipment in environments where it is crucial the cable is visible at all times. An enlightened choice in dark places.






Applications overview – Opencast

Application group		Product name	Designation	Description
MEDIUM VOLTAGE REELING CABLES				
		PROTOLON(M)	R-(N)TSCGEWOEU	MV reeling cable
		PROTOLON(M) with FO	R-(N)TSCGEWOEU	MV reeling cable with integrated fiber optic
		PROTOLON(IQ)	(N)TSKCGEWOEU	MV reeling cable with embedded sensor
MEDIUM VOLTAGE TRAILING CABLES				
		TENAX-SAS	NTSCGEWOEU	MV trailing cable abrasion and cold resistant (-50°)
		PROTOLON(SB)	NTSCGEWOEU / NTSCGECEWOEU	MV trailing cable with or without metallic screen
		PROTOLON(SB-SAM)	(N)TSCGEWOEU / (N)TSCGECEWOEU	MV trailing cable with optimized dimensions
		TENAX-LUMEN	(N)TSCGEH3S	MV trailing cable with self-illuminating function
		TENAX-PUR	(N)TSCGEH3S	MV trailing cable
MEDIUM VOLTAGE DREDGING CABLES				
		PROTOLON(ST).../3E	NTSCGEWOEU	MV water resistant cable with individual concentric earth
		PROTOLON(ST)	NTSCGEWOEU	MV water resistant cable with earth into interstices
CABLES FOR SEMI-FLEXIBLE INSTALLATION				
		PROTOLON(M)	F-(N)TSCGEWOEU	MV cable for semi-flexible use
		PROTOMONT	NSSHOEU	LV cable for semi-flexible use, water resistant
		PROTOMONT	NSHXOEU	LV cable for semi-flexible use, LSOH
		PROTOMONT(MT)	(N)SSHOEU	LV cable for semi-flexible use, with optimized dimensions
		PROTOMONT EMV-FC	(N)SSHCOEU	LV screened cable EMC compliant for VFD
		PROTOMONT EMV-FC (-45°C)	(N)SSHCOEU	LV screened cable EMC compliant for VFD, cold-resistant
MEDIUM VOLTAGE SINGLE CORE CABLES				
		FELTOFLEX	NTMCWOEU	MV single-core cable with cold removable semi-con. layer
		PROTOLON(M)	(N)TMCGCWOEU	MV single-core cable with optimized dimensions
CONTROL AND SIGNALING CABLES				
		OPTOFLEX(M)	G62.5/125, G50/125, E9/125	Flexible fibre optic cable, also suitable for underground installation
		PROTOMONT(MSR)	2YSLGCGOEU	Rubber sheathed screened data cable, also suitable for underground installation

Voltage range	Travel speed max.	Tensile force max.	Torsion max.	Sheath quality	Abrasion resistance	Water resistance	S-bend-ings in operation	Temp. range in fully flexible operation (°C)	Certificate/ Approvals
3.6/6 kV – 20/35 kV	120 m/min	25 N/mm ²	+/- 100 °/m	5GM5	Very good	Good	Multiple planes	-35 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV – 20/35 kV	120 m/min	25 N/mm ²	+/- 100 °/m	5GM5	Very good	Good	Multiple planes	-35 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV – 20/35 kV	240 m/min	30 N/mm ²	+/- 100 °/m	5GM5	Very good	Good	Multiple planes	-35 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV – 12/20 kV	–	25 N/mm ²	+/- 100 °/m	5GM5+	Excellent	Very good	–	-50 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV – 12/20 kV	–	15 N/mm ²	+/- 100 °/m*	5GM5	Very good	Very good	–	-20 to +80	VDE, MSHA, Gost-R/-K/-B, TR-CU
3.6/6 kV – 12/20 kV	–	20 N/mm ²	+/- 100 °/m*	5GM5	Very good	Very good	–	-30 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV – 12/20 kV	–	25 N/mm ²	+/- 100 °/m	PUR	Very good	Very good	–	-50 to +80	–
3.6/6 kV – 12/20 kV	–	25 N/mm ²	+/- 100 °/m	PUR	Very good	Very good	–	-50 to +80	–
1.8/3 kV – 18/30 kV	–	15 N/mm ²	+/- 25 °/m	5GM3	Good	Excellent	–	-25 to +80	Gost-R/-K/-B, TR-CU
1.8/3 kV – 18/30 kV	–	15 N/mm ²	+/- 100 °/m	5GM3	Good	Excellent	–	-25 to +80	Gost-R/-K/-B, TR-CU
1.8/3 kV – 18/30 kV	–	15 N/mm ²	+/- 100 °/m	5GM3	Good	Very good	–	-25 to +80	Gost-R/-K/-B, TR-CU
0.6/1 kV	–	15 N/mm ²	+/- 100 °/m	5GM5	Very good	Very good	–	-25 to +80	VDE, MA – China, MSHA, EAC
0.6/1 kV	–	15 N/mm ²	+/- 100 °/m	5GM3 (LSOH)	Good	Very good	–	-25 to +80	–
0.6/1 kV	–	15 N/mm ²	+/- 100 °/m	5GM5	Very good	Very good	–	-25 to +80	VDE
0.6/1 kV	–	15 N/mm ²	+/- 25 °/m	5GM5	Very good	Very good	–	-25 to +80	MSHA, EAC
0.6/1 kV	–	15 N/mm ²	+/- 25 °/m	5GM5	Very good	Very good	–	-45 to +80	MSHA, EAC
3.6/6 kV – 18/30 kV	–	15 N/mm ²	+/- 25 °/m	5GM5	Very good	Very good	–	-25 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV – 18/30 kV	–	15 N/mm ²	+/- 25 °/m	5GM3	Good	Very good	–	-25 to +80	Gost-R/-K/-B, TR-CU
–	–	max. 2000 N	+/- 100 °/m	5GM5	Very good	Very good	–	-30 to +80	–
250/250 V	–	max. 15 N/mm ²	+/- 25 °/m	EM2	Good	Good	–	-25 to +60	EAC

* +/- 25°/m if with metallic screen

Applications overview – Underground/Tunneling

Application group		Product name	Designation	Description
LOW AND MEDIUM VOLTAGE SHEARER CABLES				
		PROTOMONT(V)	NSSHCGEOEU	LV chain cable for shearers with double screen techn. and cold removable semi-con. layer
		PROTOMONT(V)	NTSKCGECWOEU	MV chain cable for shearers with double screen techn. and cold removable semi-con. layer
		PROTOMONT(VO)	(N)TSKCGEWOEU	MV chain cable for shearers with single screen techn. and cold removable semi-con. layer
		TENAX-CTE	NSSHKCGEOEU	LV chain cable for shearers with single screen techn. and semi-con. inner sheath
		PROTOMONT(Z)	NSSHKCGEOEU	LV trailing cable for shearers with double screen techn., cold removable semi-con. layer and steel armour
UNDERGROUND REELING CABLES				
		TENAX-LK	NTSKCGEWOEU	LV reeling cable with single screen techn. and semi-con. inner sheath
		PROTOMONT(S)	(N)SSHCGEOEU	LV reeling cable with single screen techn. and cold removable semi-con. layer
		CORDAFLEX(S)	NSHTOEU	LV reeling cable for fast-moving LHDs, rubber sheathed
		TROMMELFLEX M-PUR	D2X11Y	LV reeling cable for slow-moving LHDs, PUR sheathed, halogen-free
TBM REELING				
		PROTOMONT TBM	(N)TSCGECWOEU	MV reeling cable for TBMs, with double screen techn. and cold removable semi-con. layer
		PROTOMONT TBM	(N)TSCGECWHX-OEU	MV reeling cable for TBMs, with double screen techn., cold removable semi-con. layer, LSOH
		TENAX-HTT	(N)TSCGEWOEU	MV reeling cable for TBMs, with single screen techn.
CABLES FOR SEMI-FIXED INSTALLATION IN UNDERGROUND MINES AND TUNNELS				
		PROTOMONT (Festoon)	NTSKCGECWOEU	MV cable for semi-flexible use, with double screen techn. and cold removable semi-con. layer
		SUPROMONT	(N)3GHSSYCY	MV armoured cable for fixed installation, with double screen techn. and cold removable semi-con. layer
		SUPROMONT	(N)3GHSSHCH	MV armoured cable for fixed installation, with double screen techn. cold removable semi-con. layer, LSOH
		PROTOMONT(MT)	(N)SSHOEU	LV cable for semi-flexible use, with optimized dimensions
		PROTOMONT ../3E	NSSHOEU	LV cable for semi-flexible use with individual concentric earth
		PROTOMONT EMV-FC	(N)SSHCOEU	LV screened cable EMC compliant for VFD
		PROTOMONT EMV-FC (-45°C)	(N)SSHCOEU	LV screened cable EMC compliant for VFD, cold-resistant

Voltage range	Travel speed max.	Tensile force max.	Torsion max.	Sheath quality	Min. bending radii at		S-bend-ings in operation	Temp. range in fully flexible operation (°C)	Certificate/ Approvals
					max. 5N/mm²	max. 15N/mm²			
0.6/1 kV	–	15 N/mm²	+/- 25°/m	5GM5	2.3xD	5xD	–	-20 to +80	MA – China, MSHA, EAC, BAS
1.8/3 kV – 3.6/6 kV	–	15 N/mm²	+/- 25°/m	5GM5	2.3xD	5xD	–	-20 to +80	MA – China, MSHA, WUG, Gost -R/-K/-B, TR-CU
1.8/3 kV	–	15 N/mm²	+/- 50°/m	5GM3	2.3xD	5xD	–	-20 to +80	MA – China, Gost -R/-K/-B
0.6/1 kV	–	15 N/mm²	+/- 50°/m	5GM5	2.3xD	5xD	–	-20 to +80	EAC
0.6/1 kV	–	40 N/mm²	+/- 10°/m	5GM5	–	5xD	–	-20 to +80	MA – China, MSHA, EAC, BAS
0.6/1 kV	160 m/min	30 N/mm²	+/- 100°/m	5GM5	–	6xD	Multiple planes	-25 to +80	EAC
0.6/1 kV	160 m/min	30 N/mm²	+/- 50°/m	5GM5	–	6xD	Multiple planes	-25 to +80	MA – China, EAC
0.6/1 kV	160 m/min	30 N/mm²	+/- 25°/m	5GM5	–	6xD	Multiple planes	-25 to +80	MSHA, EAC
0.6/1 kV	60 m/min	25 N/mm²	+/- 50°/m	PUR (HF)	–	8xD	Single plane	-30 to +60	–
6/10 kV – 18/30 kV	30 m/min	30 N/mm²	+/- 25°/m	5GM5	–	12xD	Multiple planes	-20 to +80	Gost-R/-K/-B, TR-CU
6/10 kV – 18/30 kV	30 m/min	30 N/mm²	+/- 25°/m	5GM3 (LS0H)	–	12xD	Multiple planes	-20 to +80	Gost-R/-K/-B, TR-CU
6/10 kV – 18/30 kV	30 m/min	15 N/mm²	+/- 100°/m	5GM5	–	12xD	Multiple planes	-20 to +80	Gost-R/-K/-B, TR-CU
3.6/6 kV	–	15 N/mm²	+/- 25°/m	5GM5	–	Fix 6xD Flex 10xD	–	-25 to +80	MA – China, WUG, BAS, Gost-R/-K/-B, TR-CU
3.6/6 kV – 18/30 kV	–	15 N/mm²	+/- 25°/m	PVC YM5	–	Fix 6xD Flex 10xD	–	-5 to +60	VDE
3.6/6 kV – 18/30 kV	–	15 N/mm²	+/- 25°/m	HM4 (LS0H)	–	Fix 6xD Flex 10xD	–	-5 to +60	VDE
0.6/1 kV	–	15 N/mm²	+/- 100°/m	5GM5	–	Fix 4xD Flex 5xD	–	-25 to +80	VDE
0.6/1 kV	–	15 N/mm²	+/- 25°/m	5GM5	–	Fix 4xD Flex 5xD	–	-25 to +80	MA – China, MSHA, EAC, BAS
0.6/1 kV	–	15 N/mm²	+/- 25°/m	5GM5	–	Fix 4xD Flex 5xD	–	-25 to +80	MSHA, EAC
0.6/1 kV	–	15 N/mm²	+/- 25°/m	5GM5	–	Fix 4xD Flex 5xD	–	-45 to +80	MSHA, EAC



Türk Prysmian Kablo ve Sistemleri A.Ş.

Merkez / Headquarters

Ömerbey Mah. Bursa Asfaltı Cad.
No:51 16941 Mudanya - Bursa
T 0224 270 30 00
F 0224 270 30 24

Şube / Branch

Torun Tower - Fulya Mah. Büyükdere Cad,
Akıncı Bayırı Sokağı No: 74, Kat: 5/21
Şişli - İstanbul
T 0212 393 77 00

www.prysmian.com.tr
tpks@prysmian.com

Bizi takip edin

